

RP's information U6260631


Call out	Part Number	Description	Qty	Material
9	U6260658031	CHAISE PAD	1	Leather
12	426605RP	POLY SEAT CUSHION	1	FOAM, LMF
17	427950RP	POLY CHAISE	1	FOAM, LMF
18	427952RP	POLY OTTO	1	FOAM, LMF
34	U6260631048	COMPLETE IN/OUT BACK	1	Leather
76	U6260647337	SMALL OTTOMAN/FOOTREST UPHOL	1	Fabric
101	SBKK-3RP	(-K) SB KIT 350 25MM SP HINGE	1	Metal
102	14PWR3ZEROMKRP	-14 PWR 3-ZERO MECH	1	Metal
105	30170RP	WIDE RAIL 908	2	Metal
134	77903RP	FLOOR GLIDE	8	Plastic
145	32447RP	3ZERO MOTOR	1	Plastic, Metal
148	30383RP	POWER SUPPLY KIT W/DC CBL-1ST	1	Plastic, Metal
149	76796RP	KD BRACKET AND CLIP ASSEMBLY	2	Metal
165	32055RP3	P2/P3 HEADREST MOTOR PLASTIC MTR SHAFT	1	Plastic, Metal
173	32054RP1	P2 (THR) MECH -14 PLASTIC MTR SHAFT	1	Metal
214	74122RP	BASE CONN RIGHT (M)	1	Metal
215	74235RP	BASE CONN LHF (F)	1	Metal
218	73544RP	SPRING 11 X 28 XX 12 LP 300/B	2	Metal
225	31035RP	CENTER SEAT BUTTON LSF	1	Plastic, Metal
233	31470RP	MOTOR SCREW 20MM	8	Metal



RPs' information U6260631


Call out	Part Number	Description	Qty	Material
357	30651RP	FIBER RECYCLED BROWN	5	Fiber
419	74018RP	HDWE 1/4-20X.75 WSHRHD5/16	10	Metal
425	30030RP	1/4-20X30 UNC BLK FLT HEAD BOLT	4	Metal
426	77075RP	1-4-20X3/4 HX HD ZINC PRECT80	4	Metal
562	74019RP	HDWE 1/4-20X1.000 CN1420X1	4	Metal
653	31865RP	POWER MOTION TESTER CABLE	1	Plastic, Metal
654	32051RP	POWER MOTION TESTER LIGHT	1	Plastic, Metal





U626 Configuration 1
 Space Between Units = $\frac{3}{4}$ " for Connecting Brackets
 Unit is 3" Away From Wall

****All Measurements are Approximations****



U626 Configuration 2
 Space Between Units = $\frac{3}{4}$ " for Connecting Brackets
 Unit is 3" Away From Wall

****All Measurements are Approximations****